



UNICA®

FLEXIBLE

CLOSURE SYSTEM

The Ultimate Solution Capping For Your Wide Range Of Applications For Chemicals, Food, Lubricants & Others.

1 3-in-1 Cap with Seal Ring

Red / Blue / Black
Yellow / Green
White


CO3



5 3-in-1 Vented Cap (Ultra High Flow)

Red

CO3VUHFRD



6 4-in-1 Cap with Inner Seal Ring

White

CO4WE/COIS



7 Inner Seal

COIS



2 3-in-1 Cap with PE Gasket (Ideal for Food Application)

Red

CO3PERD



3 3-in-1 Vented Cap (Std Flow)

Red

CO3VSFRD



4 3-in-1 Vented Cap (High Flow)

Red

CO3VHFRD



Disposable Dust Cover

General Information

- Recommended closing torque for closures is 10Nm
- It is recommended to regularly check the processing parameters that have an influence on the applied torque (e.g. wrench settings, air pressure and calibration)
- Torques measured clockwise are different when measuring anti-clockwise
- Do not use any non-UNICA closures on UNICA jerricans
- Ensure jerrican threads are kept clean of fill substance before and during application torque
- Closing a jerrican that is hot to the touch requires attention to the closing tool and the temperature of the product. Temperatures above 40 degrees C will have an influence on the application and performance of the closure.
- The above recommendations are based on lab testing and market feedback

